

MODEL MINI 1 V VACUUM - GAS



OPCIÓN COMPRESOR SILENCIOSO

OPCIÓN ENROLLADOR RETALES

OPCIÓN BOMBA OXIGENO

1/2 GN 1/4 GN 1/8 GN

ESTANDAR 100

OPCIÓN

RESULTADOS DE ANALITICA OPTIMOS

0.2% O₂
19.9% CO₂

BUSCH
Vacuum Pumps and Systems

Detailed description: This advertisement for the BUSCH Model Mini 1 V Vacuum-Gas system features a central image of the main unit on the left. To its right are three optional components: a silent compressor, a trimmer, and an oxygen pump. Below these are three sets of trays labeled 1/2 GN, 1/4 GN, and 1/8 GN. A diagram shows a standard 100mm depth with an optional shallower depth. On the far right, a handheld OXYBABY analyzer is shown with a screen displaying 0.2% O₂ and 19.9% CO₂, with the text 'RESULTADOS DE ANALITICA OPTIMOS' overlaid. The BUSCH logo is in the bottom left corner.

MODEL MINI 2 V VACUUM - GAS



OPCIÓN COMPRESOR SILENCIOSO

OPCIÓN ENROLLADOR RETALES

OPCIÓN BOMBA OXIGENO

1/2 GN 1/4 GN 1/8 GN

ESTANDAR 100

OPCIÓN

RESULTADOS DE ANALITICA OPTIMOS

0.2% O₂
19.9% CO₂

BUSCH
Vacuum Pumps and Systems

Detailed description: This advertisement for the BUSCH Model Mini 2 V Vacuum-Gas system is similar to the Mini 1 V but includes additional accessories. It shows the main unit, the same three optional components, and the tray sets. The diagram also shows a shallower optional depth. The OXYBABY analyzer on the right displays the same gas percentages. The BUSCH logo is in the bottom left corner.

MODEL MAXI V VACUUM - GAS



OPCIÓN COMPRESOR SILENCIOSO

OPCIÓN ENROLLADOR RETALES

OPCIÓN BOMBA OXIGENO

1/2 GN 1/4 GN 1/8 GN

ESTANDAR 100

OPCIÓN

RESULTADOS DE ANALITICA OPTIMOS

0.2% O₂
19.9% CO₂

BUSCH
Vacuum Pumps and Systems

Detailed description: This advertisement for the BUSCH Model Maxi V Vacuum-Gas system features a larger main unit. It includes the same three optional components and tray sets as the Mini models. The diagram shows the standard 100mm depth and an optional shallower depth. The OXYBABY analyzer on the right displays the same gas percentages. The BUSCH logo is in the bottom left corner.

MODEL TSA 626 V VACIO - GAS
OPCIÓN : SKIN



MODELO TSA 826 V VACIO - GAS
OPCIÓN : SKIN

